

UltraFlux® Sealing Films

ULTRAFLUX® FOIL

- Very soft and malleable – easily takes on the shape of whatever plate it is applied to.

ULTRAFLUX® STANDARD

- Perfect choice for everyday classic PCR work.

ULTRAFLUX® RT (REAL-TIME) PRESSURE RELEASED FILM

- Highest level of clarity ideally suited for optical analysis during Real Time PCR.
- Non-tacky adhesion – only sticks when pressed against the plate surface due to the micro encapsulated beads of silicone. This film leaves no messy residue that can potentially interfere with optical analysis. Makes handling of film much easier prior to seal.



PCR

PCR Sealing Films

Item #	Seal Type	Material	Dimensions	Packaging
3640-00	UltraFlux® Foil	pierceable aluminum	total length of 5.562" (with tabs) total width of 3.25" workable length of 5.00"	100 per unit
3622-00	UltraFlux® Standard	clear polypropylene film, acrylic adhesive	total length of 5.562" (with tabs) total width of 3.13" workable length of 5.06"	100 per unit
3651-00	UltraFlux® RT (Real-Time) Pressure Released	clear polyolefin film, silicone adhesive	total length of 5.250" (with tabs) total width of 3.00" workable length of 4.63"	100 per unit

Sealing Mats (Silicone Rubber)

Item #	Description	Material	Dimensions	Packaging
3510-00	96 well sealing mat	silicone	total length of 4.67" total width of 2.90"	5 per unit, 10 units per case

ULTRAFLUX® RT FILM & PLATE BUNDLES (WITH FREE APPLICATOR)

- We have packaged our best selling UltraFlux® PCR plates with our Real-Time pressure released sealing film into convenient bundles. Each unit comes with a FREE applicator for applying the film to the plate.

Bundled Plate and Sealing Film (Includes One Applicator Per Unit)

Bundled Item #	Plate Style	Description	Packaging
3400F50	3400	96-well, unskirted standard well plate, clear, with UltraFlux® RT film	10 plates & films per unit, 10 units per case
3401F50	3401	96-well, unskirted low profile plate, clear, with UltraFlux® RT film	
3420F50	3420	96-well, semi-skirted, indented, standard well plate, clear, with UltraFlux® RT film	
3425F50	3425	96-well, semi-skirted, raised rim, standard well ABI® style plate, clear, with UltraFlux® RT film	
3426F50	3426	96-well, semi-skirted, FAST® style low profile plate, clear, with UltraFlux® RT film	
3430F50	3430	384-well, full-skirted, two-notch style plate, clear, with UltraFlux® RT film	
3430F5W	3430	384-well, full-skirted, two-notch style plate, white, with UltraFlux® RT film	
3435F50	3435	384-well, full-skirted, one-notch style plate, clear, with UltraFlux® RT film	
3535F5W	3435	384-well, full-skirted, one-notch style plate, white, with UltraFlux® RT film	
3441F50	3441	96-well, full-skirted, low profile plate, clear, with UltraFlux® RT film	
3450F50	3450	96-well, semi-skirted, standard well plate, clear, with UltraFlux® RT film	
3455F50	3455	96-well, semi-skirted, low profile, LightCycler® style plate, clear, with UltraFlux® RT film	
3455F5W	3455	96-well, semi-skirted low profile plate, white, with UltraFlux® RT film	